

Design Guidelines

Required Installation Lengths

d_N	LP Series		LK Series		Threaded Plugs DIN 908	
	d_1	l_2 min	d_1	l_4 max	d_1	l_4 max
4,0	4,40	7,0	4,0	4,0		
5,0	5,40	8,0	5,0	4,8	M8x1	11,5
6,0	6,40	8,5	6,0	5,3	M8x1	11,5
7,0	7,40	8,5	7,0	5,8	M10x1	12,0
8,0	8,45	9,5	8,0	6,8	M10x1	12,0
9,0	9,60	10,0	9,0	6,8	M12x1,5	16,0
10,0	10,65	11,0	10,0	6,8	M12x1,5	16,0
12,0	12,75	12,0	12,0	7,8	M14x1,5	16,5

d_N = given nominal bore / system bore size